

Eco-dFluxer™ SMT100 In-Line Defluxer Product# 1550

Product Description

Eco-dFluxer SMT100 is a water-based, environmentally friendly cleaner that is designed to work in both inline and batch cleaning equipment. An optimal combination of solvents and saponifiers lowers surface tension for penetration under low stand-offs, and powerful cleaning action to remove all flux residues.

Effective on a wide variety of solders and fluxes: lead, lead-free, aqueous, RMA, no clean, and new halide-free fluxes. High compatibility with common PCB metals & plastics. Eco-dFluxer SMT100 is highly filterable with long bath life. Moderate pH avoids many disposal issues.

High performance cleaning gives you brilliant solder joints and allows you to increase dilution, increase line speeds, reduce waste water, decrease cost per board, and most importantly eliminate field failures due to ionic contamination!

Drop-in replacement for semi-aqueous and aqueous cleaners. Eco-dFluxer SMT100 has been tested and proven compatible with PC-boards and all the most popular cleaning equipment: Speed line, Austin America Technologies, Aqueous Technologies and more.

Features / Benefits

- Effective on a wide variety of solders and fluxes
- Nonflammable
- Ultra rinse-able
- High compatibility with common PCB metals & plastics
- Highly concentrated – 10%-20% dilution
- Low VOC, zero GWP
- Non-ozone depleting
- Halide-Free — Prevents Ionic Contamination

Applications

- For use with in-line and batch (spray-in-air) equipment
- Dilution: 15% Eco-dFluxer SMT100 to DI water

About TECHSPRAY RENEW™

TECHSPRAY RENEW™ is a brand that represents **High Performance Eco-Cleaning™**. Techspray® has applied our expertise in solvent cleaning to formulate some of the most effective eco-friendly cleaners on the market. Performance is our top priority, using the best “green” solutions as they become available. We all are at the cusp of the ongoing movement toward sustainable products, packaging, and processes. It is Techspray’s intention to stay at the cutting-edge while keeping our products powerful and cost effective.



Chemical Properties

Properties based on diluted material, as recommended for use in in-line and batch (spray-in-air) system.

EXPOSURE LIMIT:	Limits on components not established.
Manufacturer’s recommendation	1000 ppm.
PHYSICAL STATE:	Liquid
ODOR:	Low odor
APPEARANCE:	Clear, mobile liquid
pH:	10.73 @ 15% concentration
BOILING POINT:	95°C (203°F)
FLASHPOINT AND METHOD (TAG Closed Cup):	None to boiling point
SOLUBILITY IN WATER:	Fully miscible
DENSITY:	~0.96 at 25°C (77°F)
VOC (by wt.):	12.4% by weight (EPA) @15% dilution with water.
SHelf LIFF:	5 years unopened. 2 years open

Eco-dFluxer™ SMT100 In-Line Defluxer Product# 1550

Compatibility

Eco-dFluxer SMT100 is compatible within normal operating conditions of in-line and batch (spray- in-air) cleaning and with exposed materials normally found within respective equipment.

Usage Instructions

- Recommended use concentration is 15%; Mix thoroughly with DI water.
- Used as directed in your in-line and/or batch (spray-in-air) equipment instructions.
- Higher concentration can be used to clean more difficult soils or adjust time/temperature/spray to optimize process.

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Eco-dFluxer™ SMT100 Cleaner is fully compliant with CARB (California Air Resource Board) requirements. Also compliant with European REACH (Registration, Evaluation, Authorization & Restriction of Chemicals) and WEEE (Waste Electrical and Electronic Equipment Directive) initiatives. It does not contain RoHS (Restriction of Hazardous Substances) restricted substances, SVHC (Substances of Very High Concern) list substances, or Halides.

Eco-dFluxer™ SMT100 Cleaner is Halide-Free, low VOC, zero GWP, non-Ozone depleting aqueous solution. *Refer to MSDS for additional information.*

TechLab Analysis and Capabilities

Techspray's TechLab offers a state-of-the-art cleaning, coating and analytical services to help customers optimize their processes. Cleaning equipment includes inline, batch, ultrasonic, and vapor-degreasing systems. This equipment allows us to better duplicate your production environment for process optimization and troubleshooting.

Techspray® has access to ultra-sensitive analytical equipment to not only detect contamination, but to speciate the residues to determine whether or not they may lead to current leakage, electrochemical migration, and even board failure. Testing & analytical capabilities include:

- Ion chromatography (IC) for ionic cleanliness
- SIR testing for materials and finished assemblies
- Electromigration test
- R.O.S.E. testing for general ionic measurements
- High magnification digital photo documentation

TechLab Analysis and Capabilities (Cont.)

TechLab uses a localized extraction method, which seals over troublesome areas of the board and injects high temperature steam, and then collects the affluent for analysis. This method is the most sensitive extraction process available, allowing identification of ionic contamination that other methods commonly miss.

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

Packaging and Availability

Eco-dFluxer™ SMT100 Cleaner available in the following sizes:

1550-G	1 gallon (3.8L), Makes 6.7 gal (25 L) @ 15%
1550-5G	5 gallon (19L), Makes 33.3 gal (126 L) @ 15%
1550-54G	54 gallon (205L), Makes 360 gal (1360 L) @ 15%

Defoamer DF1 : Optional Defoaming agent for Eco-dFluxer SMT100
Reduce foaming as cleaner becomes loaded to extend bath life.

- Effective at all processing temperatures
- Extends bath life
- Silicone & particulate free
- Nonflammable

1555-P	1 pint (473mL), container
---------------	---------------------------